Mis

## 1. PRODUCT IDENTIFICATION

Description

AZURE GLAZE. It belongs to high temperature glazes, with high rutile content. The result can be opaque matte, or satin. The final effect can be different depending on firing temperature, coat of glaze and kind of biscuit. The result will vary depending on the used body, temperature, cycle and atmosphere. Compound of frit: CAS N°. 65997-18-4.

Application

They can be applied by brush, spraying or dipping in single- and double-fired. For one firing it's advisable the addition of Monocol V. Temperature range 1200°C - 1340°C, recommended temperature 1260°C. It is advisable to test at extreme temperatures.

## 2. CHEMICAL COMPOSITION Metal oxides with concentrations less than 0.05% have not been determined.

Li <sub>2</sub> O	ZnO	Cr <sub>2</sub> O <sub>3</sub>	CaF <sub>2</sub>		
Na <sub>2</sub> O <b>1-5</b>	MnO	$B_2O_3$	Bi <sub>2</sub> O <sub>3</sub>	Co3O4 0.5-1	
K <sub>2</sub> O 1-5	CdO	$V_2O_5$	P <sub>2</sub> O <sub>5</sub>	MEDIUM 0-0.5	
MgO <b>0-0.5</b>	CoO	$MnO_2$	BeO	LOI 10-20	
CaO <b>10-20</b>	NiO	SiO <sub>2</sub> 40-80	CeO <sub>2</sub>	LOI 10-20	
SrO	$Al_2O_3$ <b>10-20</b>	TiO <sub>2</sub> 5-10	CuO		
BaO	Fe <sub>2</sub> O <sub>3</sub> <b>0-0.5</b>	ZrO <sub>2</sub> <b>0-0.5</b>	Pr <sub>2</sub> O <sub>3</sub>		
PbO	$Sb_2O_3$	$SnO_2$			

## **3 PHYSICAL-CHEMICAL PROPERTIES**

Aspect Grey powder

Color(fired) Blue

4. COLORIMETRY \* By Minolta ChromaControl (S)

L: 61.7 a: -2.4 b: -13.4

**5. DILATOMETRY** \* Data obtained with dilatometer BÄHR mod. DIL 801 L

(25-300)C° (50-300)C° (300-500)C° (500-600)C° Ta Transformation Ta Softening Melting point 72.6 73.9 83.2 102.6 559 C° 872 C° C°

6. GRANULOMETRIC DISTRIBUTION (WET WAY) \* Data obtained by Malvern Instruments (Master Sizer 2000)

>10μ >25μ >40μ >70μ >120μ D50μ 47.1 18.5 7.3 1.0 0.0 9.1

## 7. RECOMMENDATIONS ON GLAZED OBJECTS INTENDED FOR CULINARY USE

Formulated without lead and cadmium.

Notes: n.a (not applicable), n.d (no information available), p.n (negative tests)

